

CHEMICAL RESISTANCE HYDRA-BOY

LIST OF MATERIALS HYDRA-BOY

Tank:	PP	Suction hose:	PP, EVA
Sewage pump:	PP + GF20	Drain hose:	PP, EVA
Check valve:	PP	Floor nozzle:	PP
Screw connections:	PP	Suction tube:	PP
C-couplings:	PA6 + GF30	Suction head:	ABS

PLASTICS, MATERIAL CHARACTERISTICS | Overview of chemical resistance

EPDM	Ethylene-propylene-diene rubber	PA	Polyamide	PSU	Polysulfone
FEP	Tetrafluoroethylene-perfluoropropylene (teflon, FEP)	PC	Polycarbonate	PTFE	Polytetrafluoroethylene (teflon)
PETG	Polyethylene terephthalate	PFA	Perfluoroalkoxy (teflon, PFA)	PVC	Polyvinyl chloride
FPM/FKM	Fluorine rubber (Viton)	PMP	Polymethylpentene (TPX)	PVDF	Polyvinylidene fluoride
HDPE	High-density polyethylene	PP	Polypropylene	SAN	Styrene-acrylonitrile
LDPE	Low-density polyethylene	PS	Polystyrene	SI	Silicone rubber

Plastic abbr.	Temperature		Sterilisation ⁵⁾				Transparency	Flexibility	Specific weight g/cm ³	Water absorption %
	max. °C ¹⁾	min. °C ²⁾	Steam ⁴⁾ 121 °C	Gas ethylene oxid	Radiation 2,5 kGy	chemical formalin, ethanol				
EPDM	+ 120 °	- 30 °	yes	no	yes	yes	transparent	excellent	0.88	0.01
FEP	+ 205 °	- 255 °	yes	yes	no	yes	transparent	superb	2.15	< 0.01
FPM/FKM	+ 200 °	- 20 °					black	good	1.90	
HDPE	+ 110 °	- 50 °	no	yes	yes	yes	transparent	stiff	0.95	0.01
LDPE	+ 95 °	- 50 °	no	yes	yes	yes	transparent	excellent	0.92	0.01
PA	+ 90 °	+/- 0 °	no	yes	yes	yes	transparent	stiff	1.13	1.30
PC	+ 135 °	- 135 °	yes	yes	yes	yes	clear	rigid	1.20	0.35
PFA	+ 250 °	- 270 °	yes	yes	no	yes	transparent	excellent	2.15	0.03
PMP	+ 175 °	- 150 °	yes	yes	yes	yes	crystal clear	rigid	0.83	0.01
PP	+ 135 °	+ 5 °	yes	yes	no	yes	transparent	rigid	0.90	0.02
PS	+ 70 °	- 20 °	no	no	yes	yes	crystal clear	rigid	1.05	0.05
PSU	+ 165 °	- 100 °	yes	yes		yes	clear	stiff	1.24	0.30
PTFE	+ 270 °	- 270 °	yes	yes	no	yes	opaque	excellent	2.25	< 0.01
PVC	+ 70 °	- 30 °	no ³⁾	yes	no	yes	clear	rigid	1.35	0.06
PVDF	+ 160 °	- 40 °	yes	yes	yes	yes	transparent	rigid	1.78	0.04
SAN	+ 95 °	- 40 °	no	yes	no	yes	crystal clear	rigid	1.03	0.05
SI	+ 180 °	- 60 °	yes	yes	no	yes	transparent	excellent	1.10	
PETG	+ 70 °	+ 5 °	no	n.a.	n.a.	yes	crystal clear	rigid	1.78	0.70

1) higher in a short term

2) embrittlement temperature

3) except PVC hoses, which are resistant to steam sterilisation up to 121 °C.

4) frequent steam sterilisation leads to loss of stability!

5) clean equipment with distilled water beforehand (avoid stress corrosion cracking).

In the case of closed containers remove the closure or open it slightly; do not screw it on until it has cooled down.

Group of substances at 20 °C	ABS	ECTFE	HDPE	LDPE	PA	PC	PMP	PP	PS	PTFE/FEP/PFA	PVC	SAN	SI
Aldehydes	-	+	+	+	0	0	0	+	-	+	-	-	0
Alcohols alipathic	+	+	+	+	0	+	+	+	+	+	+	+	+
Esters	-	+	0	0	+	-	0	0	-	+	-	-	0
Ethers	-	+	0	-	+	-	-	-	-	+	-	-	-
Ketones	-	0	0	0	+	-	0	0	-	+	-	-	
Hydrocarbons													
alipathic	-	+	+	0	+	0	0	+	-	+	+	-	-
aromatic	-	+	+	0	+	-	-	0	-	+	-	-	-
halogenated	-	+	0	-	0	-	-	0	-	+	-	-	-
Acids, weak/diluted	0	+	+	+	0	0	+	+	0	+	+	0	0
Acids, strong/concentrated	-	+	+	+	-	-	+	+	0	+	+	-	-
Acids, oxidising	-	0	0	0	-	-	0	0	-	+	-	-	-
Alkalis	0	+	+	+	0	-	+	+		+	+	+	+

+ = excellent chemical resistance

Permanent exposure to the substance does not damage the plastic within 30 days. The plastic can remain resistant for years.

0 = good/conditional chemical resistance

Permanent exposure to the substance causes minor damage from approx. 7 to 30 days, which is partly reversible (softening, swelling, reduction of mechanical strength, discolouration).

- = low chemical resistance

Permanent exposure may cause immediate damage to the plastic. (Reduction of mechanical strength, deformations, discolourations, cracks, dissolution, risk of breakage).

Subject to technical changes, our terms and conditions apply: www.roessle.ag

rössle

Vacuum cleaners for fire departments